

PROCEDURE LIGHTS



Fact 7,8 Concord Cresent
Carrum Downs Vic 3201
Ph (03) 9775 0557
Fax (03) 9775 0330
web: www.het.com.au
email info@het.com.au

Model	130F	M2F	M3DF	Triaflex	Trigenflex
Light Output At 1m (in Lux.)	50,000	80,000	130,000	60,000	125,000
Colour Rendering Index Ra (Average of All Colours)	96	96	96	96	96
Colour Rendering Index R9 (Red)	92	92	92	92	92
Size of Focusable Light Spot (in cm)	14-25	14-28	12-30	12-22	15-26
Colour Temperature (in Degres Kelvin)	4300	4300	4300	4300	4300
Working Distance (in cm)	70-140	70-140	60-150	70-140	70-140
Vertical Range of Movement (in cm)	115	130	118	118	118
Number of Globes	1	1	3	3	3
Total Power Consumption (in VA)	55	80	225	120	150

Options

	No	No	Standard as Twin or Tripple	No	No
Available Camera Ready	No	No	Standard as Twin or Tripple	No	No
Available in Configuration with Monitor (Medical Grade LCD) or Monitor Bracket	Optional	Optional	Optional	Optional	Optional
Available in Configuration with Dr Mach Camera Mounted on Additional Arm	Optional	Optional	Optional	Optional	Optional
Available with Removable Sterilizable Handle	Optional	Standard	Standard	Standard	Standard
Available in Mixed/Twin/Tripple Ceiling Mounted Configutations	Yes	Yes	Yes	Yes	Yes
Available in Mobile Configuration	Yes	Yes	No	Yes	Yes
Available in Single Wall Mounted Configuration	Yes	Yes	No	Yes	Yes